


 PART NUMBER 0638L-23A
 ITEM NAME 638 NM SLM LASER (VBG DIODE; SM FIBER)

PRODUCT DATASHEET

DESCRIPTION




635 nm single longitudinal mode laser could be used in shifted excitation Raman differential spectroscopy (SERDS). Together with 633 nm SLM laser it is a perfect match for SERDS. Raman signals can be a lot easier separated from the background noise compared to conventional Raman spectroscopy. Both lasers are VBG stabilized which provides a superior center wavelength tolerance of ± 0.1 nm.

SPECIFICATIONS

Last edited on: 24 January 2019

| Parameter | Minimum Value | Typical Value | Maximum Value |
|--|---------------|---------------------------|---------------|
| Central Wavelength, nm | 637.7 | 637.8 | 638.1 |
| Longitudinal modes | - | Single | - |
| Spectral line width FWHM, pm | - | 0.1 ¹ | 1 |
| Output power, mW | - | 60 ² | - |
| Side-mode suppression ratio (SMSR), dB | 40 | 50 | 60 |
| Power stability, % (RMS, 8 hrs) | - | 1 ³ | 2 |
| Power stability, % (peak-to-peak, 8 hrs) | - | 2 ⁴ | 3 |
| Noise, % (RMS, 20 Hz to 20 MHz) | - | 0.25 ⁵ | 0.6 |
| Control interface type | - | UART/USB | - |
| Operation mode | - | APC (CW) | - |
| Modulation bandwidth, MHz | - | N/A ⁶ | - |
| Input voltage, VDC | 4.8 | 5 | 5.3 |
| External power supply requirement | - | +5 V DC, 1.5 A | - |
| Dimensions, mm | - | 50 x 30 x 18 ⁷ | - |
| Fiber Length, m | 0.95 | 1 | 1.1 |
| Heat-sinking requirement, °C/W | - | 1 | - |
| Optimum heatsink temperature, °C | 15 | 20 | 30 |
| Warm up time, mins (cold start) | 0.2 | 1 | 2 |
| Temperature stabilization | - | Yes | - |
| Overheat protection | - | Yes | - |
| Storage temperature, °C (non-condensing) | -10 | - | 50 |
| Net weight, kg | 0.1 | 0.12 | 0.14 |

TYPICAL SPECTRUM



Typical spectrum of 0638 nm diode laser. Measured with 20 pm resolution.

| | | | |
|-----------------------------------|-----|---|----|
| Max. power consumption, W | 0.4 | 2 | 10 |
| Warranty, months (op. hrs) | - | 14 (10000) ⁸ | - |
| RoHS | - | Yes | - |
| CE compliance | - | - General Product Safety Directive (GPSD) 2001/95/EC - (EMC) Directive 2004/108/EC | - |
| Laser Safety Class | - | 3B | - |
| OEM lasers are not compliant with | - | IEC60825-1:2014 (compliant using additional accessories) | - |
| Country of origin | - | Lithuania | - |

¹ Measured with a scanning Fabry-Perot interferometer having 7.5 Mhz resolution, with scanning frequency of about 10 Hz. Interferometer testing is not provided for each laser being manufactured, the standard test is OSA measurement with 10-20 pm resolution instead.

² The output power of SLM lasers shall not be tuned and SLM performance is not guaranteed at power ratings other than factory preset. However, the power setting capability is not disabled. External attenuators are recommended instead

³ Long term power test is carried out using an optical power meter with an input bandwidth of 10 Hz. Actual measurement rate has a period of about 20 seconds to 1 minute.

⁴ Long term power test is carried out using an optical power meter with an input bandwidth of 10 Hz. Actual measurement rate has a period of about 20 seconds to 1 minute.

⁵ Noise level is measured with a fast photodiode connected to an oscilloscope. The overall system bandwidth is from 2 kHz to 20 MHz.

⁶ SLM lasers shall not be modulated - use external modulators instead.

⁷ Excluding control interface pins and an output window/fiber assembly.

⁸ Whichever occurs first. The laser has an integrated operational hours counter.

Note: Product specifications are subject to change without prior notice to improve reliability, function or design or otherwise.